

MACROLEX® Yellow 6G

Colour Index Part I Solvent Yellow 179; Disperse Yellow 201

Part II

Chemical description Methine dyestuff

Form supplied powder

Shade yellow with a green cast

1/3 Standard depth 0.36% dyestuff (determined in GP-PS with 2% TiO₂)

Density (23°C) approx. 1.13 g/cm3

Bulk density approx. 0.21 g/cm³ (according to DIN ISO 787-11)

Melting point approx. 115°C

Main fields of application Transparent and opaque dyeing of PC, PET, ABS and

ABS / PC blends.

Storage stability 60 months from delivery ex plant LANXESS Deutschland GmbH

Solubility in q/l at temperature 23°C (approximate figures)

	•				<u> </u>				
Water	Acetone	Benzyl alcohol	Butyl acetate	Ethanol	Methyl methacrylate	Methylene chloride	Styrene (monomer)	Xylene	
insoluble	200	65	90	2.0	120	550	340	130	

in °C at 1/3 standard depth with 1% TiO2 (ABS 4% TiO2 and PS 2% TiO2) evaluated **Heat stability** according to DIN EN 12877; (approximate figures)

PS	SB*	ABS	SAN	PMMA	PC	PA 6	PA 6.6	PET	PBT
300	300	260	300	300	350	•	•	290	280

^{*} For Styrene-butadiene block copolymer the use of this dye is not recommended.

Lightfastness 1% TiO₂ (PS 2% TiO₂) standard depth with DIN EN ISO 4892-2; transparent coloration with 0.05% dye; evaluated with 8-step

blue wool scale

	PC			PS		PMMA			
Dye content in %	reduction	transparent	Dye content in %	reduction	transparent	Dye content in %	reduction	transparent	
0.070	7	8	0.360	6-7	8	0.070	6-7	8	

Materials used for testing of Heat stability and Lightfastness:

PS: BASF Polystyrene 143E PA 6: LANXESS Durethan B30S SB: BASF Polystyrene 472C PA 6.6: LANXESS Durethan A30H 1.0

Page 1 of 3 Edition: 22. Sep 2016



Technical Data Sheet



ABS: LANXESS Novodur P2X PET: Voridian 9921 W

SAN: BASF Luran 368R PBT: LANXESS Pocan B1505 PMMA: Röhm Plexiglas 7H TiO₂: Kerr McGee Tronox R-FK-3

PC: Bayer MaterialScience Makrolon 2800

The test result were evaluated with the above mentioned conditions and materials. For other polymers, polymergrades, TiO₂ grades and dyes concentrations, the results can be different from the values above.

Fastness to bleeding


(Suitability for dyeing household utensils)

No staining of distilled water, 2% by weight acetic acid, 10% by volume ethanol, coconut oil or peanut oil in our test on 0.1% dyeing of PS, ABS, SAN, PMMA, PC, PET and PVC-U. The tests were carried out in accordance with the recommendations of the German BfR [for plastic applications (saturated strips of filter paper, 5h at 50°C)].

Purity

This dyestuff meets current purity requirements for dyeing household utensils and toys in Europe.

Transmission curve MACROLEX Yellow 6G in GP-PS (2mm thickness)





Reflection curve MACROLEX Yellow 6G in GP-PS

Page 2 of 3 Edition: 22. Sep 2016 X

Technical Data Sheet







This information and our technical advice - whether verbal, in writing or by way of trials - are given in good faith but without warranty, and this also applies where proprietary rights of third parties are involved. Our advice does not release you from the obligation to verify the information currently provided - especially that contained in our safety data and technical information sheets - and to test our products as to their suitability for the intended processes and uses. The application, use and processing of our products and the products manufactured by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. Our products are sold in accordance with the current version of our General Conditions of Sale and Delivery.



LANXESS Deutschland GmbH Business Unit Rhein Chemie Additives Kennedyplatz 1 50569 Cologne, Germany http://rch.lanxess.com

Page 3 of 3 Edition: 22. Sep 2016

